

**TCMT indexable insert for finishing 30 pieces, HB7020-2, Size: 110202****Order data**

Order number	GG2840 110202
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.4 mm
Feed f	0.07 - 0.25 mm/rev.
Contents	260950 HB7020-2
ISO code indexable insert	TCMT 110202
Cutting depth $a_{p \max}$	2.75 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Main application	P
Number of changes/inserts	3
Cutting speed v_c main application	140 - 400 mm/min
Cutting depth a_p	0.2 - 1.5 mm

Data sheet

Cutting depth $a_{p \min}$	0.25 mm
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2840 110202