



Value pack DCMT indexable insert finishing 30 pieces



Order data

Order number	GG2626 11T302
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.05 - 0.2 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	2.75 mm
Tool material	Carbide
ISO code indexable insert	DCMT 11T302
Corner radius	0.2 mm
Coating	TiCN
Contents	260377 HBT130
Cutting depth a_p	0.1 - 1 mm
Cutting speed v_c main application	60 - 220 mm/min
Number of changes/inserts	2

Data sheet

Main application	M
Finishing/roughing assignment	Finishing
Quantity	30
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MF
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2626 11T302