


WNMG indexable insert for finishing 30 pieces, HBT130, Size: 060404

Order data

Order number	GG3982 060404
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth $a_{p \max}$	2 mm
Contents	251938 HBT130
Cutting speed v_c main application	60 - 220 mm/min
Number of changes/inserts	6
Coating	TiCN
Feed f	0.15 - 0.45 mm/rev.
Quantity	30
ISO code indexable insert	WNMG 060404
Corner radius	0.4 mm

Data sheet

Cutting depth a_p	0.5 - 2 mm
Tool material	Carbide
Main application	M
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MF
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3982 060404