

**Value pack CNMG indexable insert medium machining 30 pieces HB7020-2****Order data**

Order number	GG2408 120404
GTIN	4067263092292
Item class	GGN

Technical description

Number of changes/inserts	4
Cutting speed v_c main application	130 - 370 mm/min
Tool material	Carbide
Cutting depth a_p	0.3 - 4 mm
Corner radius	0.4 mm
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Main application	P
ISO code indexable insert	CNMG 120404
Feed f	0.2 - 0.5 mm/rev.
Cutting depth $a_{p \max}$	4.25 mm

Data sheet

Contents	250156 HB7020-2
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2408 120404