

**CCMT indexable insert for medium machining 50 pieces, HB7020-2, Size: 09T304****Order data**

Order number	GG2811 09T304
GTIN	4067263095200
Item class	GGN

Technical description

Number of changes/inserts	2
Contents	260150 HB7020-2
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
ISO code indexable insert	CCMT 09T304
Cutting speed v_c main application	110 - 350 mm/min
Tool material	Carbide
Cutting depth $a_{p \max}$	3.25 mm
Feed f	0.08 - 0.3 mm/rev.

Data sheet

Main application	P
Finishing/roughing assignment	Finishing
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2811 09T304