

**TCMT indexable insert for medium machining 30 pieces, HB7010-2, Size: 110202****Order data**

Order number	GG2845 110202
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Number of changes/inserts	3
Feed f	0.08 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 440 mm/min
Cutting depth $a_{p \text{ min}}$	0.15 mm
ISO code indexable insert	TCMT 110202
Contents	260980 HB7010-2
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \text{ max}}$	2.75 mm
Tool material	Carbide

Data sheet

Corner radius	0.2 mm
Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2845 110202