

**Hand tap set, uncoated, MF: 14X1,5****Order data**

Order number	130500 14X1,5
GTIN	4067263036388
Item class	12G

Description**Version:**

2-piece set **comprising taper and plug tap.**

Thread ground from solid and relief ground.

Technical description

Thread type	MF
Tool material	HSS
Thread depth	28 mm
Shank Ø D _s	11 mm
Tolerance class	ISO 2 6H
Thread size	M14×1.5
Standard	DIN 2181
Shank square □	9 mm

Tapping hole Ø	12.5 mm
Thread Ø	14 mm
Thread pitch	1.5 mm
Overall length L	70 mm
Coating	uncoated
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Serial hand taps
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
GG(G)	suitable only under restricted conditions		

Data sheet

Uni	suitable
Oil	suitable
dry	suitable only under restricted conditions