

**Value pack WNMG indexable insert finishing 30 pieces HB7035-2****Order data**

Order number	GG2480 080408
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	WNMG 080408
Cutting depth a_p	0.3 - 2 mm
Main application	P
Cutting depth $a_{p \max}$	2.75 mm
Contents	251964 HB7035-2
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	150 - 350 mm/min
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.1 - 0.4 mm/rev.
Number of changes/inserts	6
Tool material	Carbide
Corner radius	0.8 mm
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2480 080408
