


TCMT indexable insert for finishing 50 pieces, HBT020, Size: 16T304

Order data

Order number	GG3945 16T304
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	3
ISO code indexable insert	TCMT 16T304
Main application	P
Corner radius	0.4 mm
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.1 - 0.3 mm/rev.
Contents	260968 HBT020
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting speed v_c main application	120 - 330 mm/min
Cutting depth a_p	0.4 - 1.5 mm

Data sheet

Quantity	50
Coating	TiCN
Cutting depth $a_{p \max}$	4 mm
Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PF
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3945 16T304