

**VBMT indexable insert for finishing 30 pieces, HB7010-2, Size: 160404****Order data**

Order number	GG2852 160404
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Number of changes/inserts	2
Cutting depth $a_{p \max}$	2.5 mm
Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
Tool material	Carbide
ISO code indexable insert	VBMT 160404
Main application	P
Cutting speed v_c main application	150 - 500 mm/min
Cutting depth a_p	0.2 - 1.5 mm
Feed f	0.07 - 0.25 mm/rev.

Data sheet

Contents	261152 HB7010-2
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2852 160404