

**CCMT indexable insert for medium machining 50 pieces, HB7130-2, Size: 120408****Order data**

Order number	GG3510 120408
GTIN	4067263096221
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.55 mm
Quantity	50
Cutting depth $a_{p \max}$	4.25 mm
Feed f	0.1 - 0.4 mm/rev.
Number of changes/inserts	2
Main application	M
Cutting speed v_c main application	70 - 240 mm/min
Contents	260160 HB7130-2
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm

Data sheet

Tool material	Carbide
Cutting depth a_p	0.2 - 4 mm
ISO code indexable insert	CCMT 120408
Tolerance	M
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3510 120408