

**TCMT indexable insert for finishing 30 pieces, HB7120-1, Size: 110208****Order data**

Order number	GG3540 110208
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Contents	260954 HB7120-1
Number of changes/inserts	3
Cutting depth a_p	0.2 - 1.5 mm
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Feed f	0.1 - 0.3 mm/rev.
Cutting depth $a_{p \min}$	0.5 mm
Cutting depth $a_{p \max}$	2.75 mm
ISO code indexable insert	TCMT 110208
Main application	M
Cutting speed v_c main application	90 - 290 mm/min
Quantity	30
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3540 110208
