

**SNMG indexable insert for medium machining 30 pieces, HB7120-1, Size: 120404****Order data**

Order number	GG2944 120404
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	8
Cutting depth a_p	0.5 - 4 mm
Cutting depth $a_{p \max}$	4:25 mm
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
ISO code indexable insert	SNMG 120404
Contents	251222 HB7120-1
Main application	M
Feed f	0.1 - 0.4 mm/rev.
Tool material	Carbide
Cutting depth $a_{p \min}$	0.25 mm
Cutting speed v_c main application	80 - 260 mm/min
Quantity	30
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2944 120404
