

**CCMT indexable insert for finishing 50 pieces, HB7120-1, Size: 060204****Order data**

Order number	GG3503 060204
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.4 mm
Cutting depth $a_{p \max}$	2 mm
Quantity	50
Cutting depth a_p	0.2 - 2.5 mm
Tolerance	M
Tool material	Carbide
Main application	M
Cutting speed v_c main application	90 - 290 mm/min
Feed f	0.1 - 0.3 mm/rev.
Number of changes/inserts	2
ISO code indexable insert	CCMT 060204
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Contents	260052 HB7120-1
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3503 060204
