

Garant**WNMG indexable insert for medium machining 50 pieces, HB7140-2, Size: 060404****Order data**

Order number	GG2987 060404
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	WNMG 060404
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	6
Tolerance	M
Coating	coated
Contents	252062 HB7140-2
Tool material	Carbide
Corner radius	0.4 mm
Main application	M
Cutting speed v_c main application	60 - 200 mm/min

Data sheet

Cutting depth $a_{p \max}$	2 mm
Feed f	0.1 - 0.5 mm/rev.
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.5 - 4 mm
Quantity	50
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2987 060404