

**CCGT indexable insert for medium machining 50 pieces, HU7310, Size: 09T304****Order data**

Order number	GG3806 09T304
GTIN	4067263097501
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Feed f	0.05 - 0.5 mm/rev.
Number of changes/inserts	2
Tool material	Carbide
Cutting depth a_p	0.1 - 4 mm
Main application	N
Corner radius	0.4 mm
Cutting depth $a_{p \min}$	0.25 mm
ISO code indexable insert	CCGT 09T304
Cutting depth $a_{p \max}$	3.25 mm
Cutting speed v_c main application	350 - 600 mm/min
Contents	260150 HU7310
Coating	uncoated
Quantity	50
Tolerance	G
Type	HU7310
Cutting conditions	continuous

Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3806 09T304