

Garant**DNMG indexable insert for medium machining 50 pieces, HB7020-2, Size: 150608****Order data**

Order number	GG2429 150608
GTIN	4067263092889
Item class	GGN

Technical description

Tool material	Carbide
Cutting depth a_p	0.3 - 4 mm
Main application	P
Cutting speed v_c main application	130 - 370 mm/min
Number of changes/inserts	4
Contents	250762 HB7020-2
Cutting depth $a_{p \min}$	0.55 mm
ISO code indexable insert	DNMG 150608
Cutting depth $a_{p \max}$	3.75 mm
Finishing/roughing assignment	Finishing

Data sheet

Corner radius	0.8 mm
Feed f	0.2 - 0.5 mm/rev.
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2429 150608