


WNMG indexable insert for finishing 30 pieces, HB7130-2, Size: 060408
Order data

Order number	GG2977 060408
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	WNMG 060408
Finishing/roughing assignment	Finishing
Number of changes/inserts	6
Cutting depth $a_{p \min}$	0.25 mm
Tool material	Carbide
Cutting depth a_p	0.3 - 2 mm
Cutting speed v_c main application	80 - 270 mm/min
Feed f	0.1 - 0.4 mm/rev.
Quantity	30
Cutting depth $a_{p \max}$	2.75 mm
Corner radius	0.8 mm
Coating	coated
Main application	M
Contents	251954 HB7130-2
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2977 060408
