

**CNMG indexable insert for medium machining 50 pieces, HB7120-1, Size: 09T308****Order data**

Order number	GG2909 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Tool material	Carbide
Main application	M
Contents	250152 HB7120-1
ISO code indexable insert	CNMG 09T308
Cutting depth a_p	0.5 - 4 mm
Quantity	50
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Number of changes/inserts	4
Cutting depth $a_{p \max}$	3:25 mm
Feed f	0.1 - 0.4 mm/rev.
Tolerance	M
Cutting depth $a_{p \min}$	0.55 mm
Cutting speed v_c main application	80 - 260 mm/min
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG2909 09T308
