



Value pack SNMG indexable insert finishing 30 pieces HB7020-2



Order data

Order number	GG2441 120408
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \max}$	4.25 mm
Main application	P
ISO code indexable insert	SNMG 120408
Corner radius	0.8 mm
Feed f	0.1 - 0.4 mm/rev.
Tool material	Carbide
Cutting speed v_c main application	160 - 400 mm/min
Contents	251144 HB7020-2
Cutting depth $a_{p \min}$	0.55 mm

Data sheet

Number of changes/inserts	8
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2441 120408