



Value pack GARANT Vap Tap machine tap HSS-E Form C, 5 pieces



Order data

Order number	GG1358 M3
GTIN	4069515046442
Item class	GGN

Description

Version:

GARANT Vap Tap general-purpose tap. Can be used **reliably** in a **wide range of materials**. Optimised **neck and flute length** for **improved chip evacuation** when working on **deep** threads. High-performance **HSS-E tool material** with higher **vanadium content** for improved **wear resistance**. **Surface vapourised** for reduced edge build-up.

Same as number: 135805.

Note:

Up to \leq M16: contents 5 pcs. per set.

From \geq M18: contents 3 pcs. per set.

Technical description

Thread pitch	0.5 mm
Shank square <input type="checkbox"/>	2.7 mm
Thread type	M
Standard	DIN 371
Overall length L	56 mm
Tool material	HSS E

Data sheet

Shank Ø D _s	3.5 mm
Contents	5
Tapping hole Ø	2.5 mm
Thread size	M3
Number of cutting edges Z	3
Number of clamping slots	3
Thread Ø	3 mm
Tolerance class	ISO 2 6H
Thread depth	9 mm
Coating	vaporised
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Helix angle	40 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Vap Tap
Type of product	Taps

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	18 m/min	N
Aluminium (short chipping)	suitable	13 m/min	N
Steel < 500 N/mm ²	suitable	18 m/min	P

Data sheet

Steel < 750 N/mm ²	suitable	15 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Steel < 1100 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable	6 m/min	M
CuZn	suitable only under restricted conditions	15 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		

Suitable products

No Shop URL available for: GG1358 M3