

### Computer workstation with printer flap, mobile, Type: GB



#### Order data

|              |               |
|--------------|---------------|
| Order number | 948262 GB     |
| GTIN         | 4062406074616 |
| Item class   | 9GS           |

#### Description

##### Version:

Computer cabinet with separately lockable double-leaf door with polycarbonate window or with printer flap. Fitted with partition for the tower compartment with galvanised storage shelf, pull-out shelf (load capacity 45 kg) with strain relief. Keyboard drawer with recessed and removable storage tray, palm rest made from bamboo and strain relief. Locking with a common key. Cable pass-through on the rear of the housing. Storage shelf made of bamboo.

With mobile base composed of 2 fixed wheels and 2 electrically conductive castors with brakes Ø 125 mm and push handles.

With space-saving TFT monitor housing for flat screens, lockable, with storage compartment for cables. Self-supporting steplessly adjustable lift door with polycarbonate window.

##### Colour:

Body and keyboard drawer RAL 7035 light grey, doors, drawer front and pull-out shelf RAL 7016 anthracite **powder-coated**.

#### Technical description

|                         |            |
|-------------------------|------------|
| Dimensions printer flap | 346×290 mm |
| Depth                   | 700 mm     |

|                                    |                                  |
|------------------------------------|----------------------------------|
| Monitor housing usable height      | 460 mm                           |
| Width in G                         | 40                               |
| Weight                             | 120 kg                           |
| Height                             | 1770 mm                          |
| Monitor housing usable width       | 690 mm                           |
| Monitor housing usable depth       | 230 mm                           |
| Depth in G                         | 28                               |
| Width                              | 1000 mm                          |
| Support cabinet usable width right | 223 mm                           |
| Support cabinet usable width left  | 700 mm                           |
| Support cabinet usable height      | 645 mm                           |
| On/Off switch                      | yes                              |
| Nominal voltage                    | 250 V                            |
| #Plug type, input                  | G                                |
| Wheel Ø                            | 125 mm                           |
| Material thickness                 | 0.9 mm                           |
| Door opening angle                 | 250 degrees                      |
| Cylinder lock                      | modular barrel                   |
| Colour selection                   | RAL 9002, 7035, 7016, 5012, 5005 |
| Type of product                    | Computer workstation             |

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/948262-GB>