

**CNMG indexable insert for medium machining 30 pieces, HB7130-2, Size: 120412****Order data**

Order number	GG2907 120412
GTIN	4067263093855
Item class	GGN

Technical description

Cutting speed v_c main application	70 - 240 mm/min
Cutting depth a_p	0.5 - 4 mm
Cutting depth $a_{p \max}$	4:25 mm
Main application	M
Tool material	Carbide
Finishing/roughing assignment	Finishing
Quantity	30
Tolerance	M
Corner radius	1.2 mm
ISO code indexable insert	CNMG 120412

Data sheet

Number of changes/inserts	4
Contents	250160 HB7130-2
Feed f	0.1 - 0.4 mm/rev.
Cutting depth $a_{p \min}$	0.8 mm
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2907 120412