

**DCGT indexable insert for medium machining 50 pieces, HU7310, Size: 070202****Order data**

Order number	GG3817 070202
GTIN	4067263097860
Item class	GGN

Technical description

Tool material	Carbide
ISO code indexable insert	DCGT 070202
Cutting depth a_p	0.1 - 4 mm
Number of changes/inserts	2
Feed f	0.05 - 0.5 mm/rev.
Quantity	50
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	350 - 600 mm/min
Cutting depth $a_{p \max}$	1.75 mm
Coating	uncoated
Corner radius	0.2 mm
Contents	260449 HU7310
Cutting depth $a_{p \min}$	0.15 mm
Main application	N
Tolerance	G
Type	HU7310

Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3817 070202