

Garant**DNMG indexable insert for roughing 50 pieces, HB7020-2, Size: 150608****Order data**

Order number	GG2436 150608
GTIN	4067263093008
Item class	GGN

Technical description

Number of changes/inserts	4
Tool material	Carbide
Main application	P
Cutting depth $a_{p \min}$	0.55 mm
Cutting speed v_c main application	110 - 360 mm/min
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Cutting depth a_p	1.5 - 6 mm
Contents	250862 HB7020-2
Cutting depth $a_{p \max}$	3.75 mm
ISO code indexable insert	DNMG 150608

Data sheet

Feed f	0.25 - 0.6 mm/rev.
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2436 150608