


**WNMG indexable insert for medium machining 50 pieces, HBT130, Size: 060404****Order data**

Order number	GG3985 060404
GTIN	4067263095002
Item class	GGN

Technical description

Cutting speed v_c main application	50 - 200 mm/min
Number of changes/inserts	6
ISO code indexable insert	WNMG 080404
Feed f	0.12 - 0.45 mm/rev.
Cutting depth $a_{p \text{ min}}$	0.25 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \text{ max}}$	2 mm
Contents	252092 HBT130
Cutting depth a_p	0.5 - 5 mm
Quantity	50

Main application	M
Coating	TiCN
Tool material	Carbide
Corner radius	0.4 mm
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3985 060404