

**Garant****T-tap wrench with ratchet, All-steel, Overall length: 110mm**

## Order data

|              |               |
|--------------|---------------|
| Order number | 148700 110    |
| GTIN         | 4045197511119 |
| Item class   | 11K           |

## Description

### Version:

With two-jaw chuck for clamping square shanks. Moveable T-handle with a groove at each end for engaging the retaining ball. Bracket chrome-plated. Ratchet is reversible and can also be locked. **All-steel construction** for high torque applications. Toolholder with precision concentricity and tight tolerances. Clamping jaws milled and induction hardened for high toughness and optimum surface hardness. Patented clamping jaw shape also allows precise and secure clamping of taps even with 1/4 inch hexagon shanks (e.g. No. 676307). Clamps on the complete hexagon face.

### Application:

Suitable for tapping holes where access is difficult.

### Note:

The square sizes of other tap and reamer sizes can be found in the tables in the respective Product Groups.

## Technical description

|                                   |            |
|-----------------------------------|------------|
| for hand taps DIN 352             | M4,5 – M12 |
| Capacity <input type="checkbox"/> | 4.6 - 8 mm |

|                            |           |
|----------------------------|-----------|
| Overall length             | 110 mm    |
| Spare jaws No. 148710 size | 110       |
| Material                   | All-steel |
| Type of product            | Pin vice  |