

**Garant**

**Short drill chuck Form A, HSK-A 63, Clamping range: 0,3-8mm**



**Order data**

|              |               |
|--------------|---------------|
| Order number | 307725 0,3-8  |
| GTIN         | 4045197931863 |
| Item class   | 31B           |

**Description**

**Version:**

- **For clockwise and anticlockwise rotation.**
- **With RFID/Balluffchip bore.**

With through coolant feed up to max. 50 bar.

Concentricity  $\leq 20 \mu\text{m}$ .

- **Slim design.**
- **Specific coolant transfer to tools with IC.**
- **Optimum holding torques at the tool.**

**Supplied with:**

**Clamping wrench** with T-handle.

**Optional extras:**

Socket wrench No. 309890. Coolant tube No. 309880.

**Technical description**

|                          |            |
|--------------------------|------------|
| Clamping range           | 0.3 - 8 mm |
| External $\varnothing$ D | 35 mm      |

|                                        |                       |
|----------------------------------------|-----------------------|
| Overhang dimension A                   | 93 mm                 |
| Spare Torx® chuck key No. 625220       | TX25                  |
| Type                                   | slim                  |
| Adapter                                | HSK-A 63              |
| Arbor standard                         | ISO 12164-1           |
| Arbor standard                         | DIN 69882-7           |
| Arbor standard                         | DIN 69893-1           |
| Shape                                  | A                     |
| Through-coolant                        | yes, with max. 50 bar |
| Balance quality G at rotational speed  | G 2.5 at 25,000 rpm   |
| Concentricity                          | ≤ 20 µm               |
| maximum tightening torque $M_{d\ max}$ | ≤ 14 Nm               |
| Type of product                        | Short drill chuck     |

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/307725-0,3-8>