



Value pack CNMG indexable insert medium machining 30 pieces HB7020-2



Order data

Order number	GG2408 120412
GTIN	4067263092339
Item class	GGN

Technical description

Tool material	Carbide
ISO code indexable insert	CNMG 120412
Cutting depth a_p	0.3 - 4 mm
Main application	P
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	130 - 370 mm/min
Contents	250160 HB7020-2
Cutting depth $a_{p \max}$	4.25 mm
Cutting depth $a_{p \min}$	0.8 mm
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	4

Corner radius	1.2 mm
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2408 120412