

**DCGT indexable insert for finishing 50 pieces, HB7315-1, Size: 070204****Order data**

Order number	GG3813 070204
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	1.75 mm
Main application	N
Quantity	50
Number of changes/inserts	2
Contents	260353 HB7315-1
Corner radius	0.4 mm
Cutting depth a_p	0.05 - 0.6 mm
ISO code indexable insert	DCGT 070204
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.03 - 0.1 mm/rev.
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting speed v_c main application	120 - 600 mm/min
Tolerance	G
Type	HB7315-1
Cutting conditions	continuous
Chip breaker	AF
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3813 070204
