

**CNMG indexable insert for roughing 30 pieces, HB7120-1, Size: 120412****Order data**

Order number	GG2912 120412
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	70 - 240 mm/min
Cutting depth $a_{p \min}$	0.8 mm
ISO code indexable insert	CNMG 120412
Finishing/roughing assignment	Roughing
Main application	M
Tool material	Carbide
Corner radius	1.2 mm
Number of changes/inserts	4
Cutting depth $a_{p \max}$	4:25 mm
Cutting depth a_p	1.5 - 6 mm
Contents	250324 HB7120-1
Feed f	0.25 - 0.6 mm/rev.
Quantity	30
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2912 120412
