

Garant**WNMG indexable insert for finishing 50 pieces, HB7120-1, Size: 060408****Order data**

Order number	GG2979 060408
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.8 mm
Contents	251954 HB7120-1
Feed f	0.1 - 0.4 mm/rev.
ISO code indexable insert	WNMG 060408
Cutting depth a_p	0.3 - 2 mm
Tool material	Carbide
Number of changes/inserts	6
Main application	M
Cutting depth $a_{p \max}$	2 mm
Cutting speed v_c main application	90 - 290 mm/min
Cutting depth $a_{p \min}$	0.55 mm
Finishing/roughing assignment	Finishing
Quantity	50

Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2979 060408