

**CNMG indexable insert for medium machining 50 pieces, HB7020-2, Size: 120404****Order data**

Order number	GG2411 120404
GTIN	4067263092308
Item class	GGN

Technical description

Contents	250156 HB7020-2
Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.3 - 4 mm
Main application	P
Cutting depth $a_{p \max}$	4.25 mm
Tool material	Carbide
Number of changes/inserts	4
ISO code indexable insert	CNMG 120404
Corner radius	0.4 mm
Cutting depth $a_{p \min}$	0.25 mm

Finishing/roughing assignment	Finishing
Cutting speed v_c main application	130 - 370 mm/min
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2411 120404