



ER clamping nut with radial run-out adjustment, for ER: 25



Order data

Order number	309619 25
GTIN	2050002004023
Item class	33E

Description

Version:

Thread and taper ground in a single setup for highest concentricity.
6 screws allow the radial run-out to be reduced to zero.

Suitable for:

All standard ER collet chucks.
Ideally suitable for lathes, both for stationary and driven tools.

Optional extras:

ER clamping wrench, No. 309680 – 309740.
Single open ended spanner (for size 16), No. 613300 size 25.

Note:

Collet chuck and clamping nut are balanced separately!
Up to 6000 rpm.

Technical description

External Ø D	50 mm
Thread	M32×1.5

Data sheet

for ER	25 mm
Overall length L	21.8 mm
Standard	DIN 6499 D
Type of product	Clamping nut