



VCMT indexable insert for medium machining 30 pieces, HBT130, Size: 110304

Order data

Order number	GG2695 110304
GTIN	4067263097273
Item class	GGN

Technical description

Tool material	Carbide
ISO code indexable insert	VCMT 110304
Cutting depth $a_{p \max}$	1.75 mm
Main application	M
Coating	TiCN
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 2.5 mm
Cutting speed v_c main application	50 - 200 mm/min
Contents	261472 HBT130
Corner radius	0.4 mm
Feed f	0.05 - 0.35 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Quantity	30
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG2695 110304
