

**CNMG indexable insert for medium machining 50 pieces, HB7035-2, Size: 120408****Order data**

Order number	GG2412 120408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	4.25 mm
Feed f	0.2 - 0.5 mm/rev.
Tool material	Carbide
ISO code indexable insert	CNMG 120408
Corner radius	0.8 mm
Cutting depth a_p	0.3 - 4 mm
Main application	P
Contents	250158 HB7035-2
Number of changes/inserts	4
Cutting depth $a_{p \min}$	0.55 mm

Data sheet

Cutting speed v_c main application	120 - 320 mm/min
Finishing/roughing assignment	Finishing
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2412 120408