

Garant**Softcut® shoulder mill with plain shank, for indexable inserts AP..****Order data**

Order number	215609 10/2
GTIN	4045197409775
Item class	210

Description**Version:**

High precision indexable shoulder mill with irregular pitch for very smooth cutting, very high precision and very high metal removal rate. **New generation** of high performance indexable shoulder mills **with special geometry for reduced cutting forces for MTC applications** under **unstable conditions** or **for spindles with low drive power**. **Suitable inserts APMT 0602..**

Application:

For shoulder milling to large depths, also slotting. General use in all steels including stainless and acid-resistant steels.

Spare part:

Pack of insert screws No. 219827 (6IP; 0.45 Nm).

Note:

GARANT torque screwdriver TQ No. **211750 size 0.45**, use bit No. **674252 size 6IP**.
The insert pocket must be modified when using indexable inserts with a radius of 2 mm.

Technical description

Set of insert screws	219827 (6IP; 0.45 Nm)
Shank $\varnothing D_s$ h6	10 mm
Overall length L_{tot}	57 mm
Cutting edge $\varnothing D_c$	10 mm
Overhang L_1	17 mm
suitable indexable insert	AP.. 0602..
Number of cutting edges Z	2

Ramping length L for α_{\max}	6.85 mm
Circular interpolation milling $\varnothing D_{\max}$	18 mm
Circular interpolation milling $\varnothing D_{\min}$	18 mm
Circular interpolation milling a_p	0.7 mm
Ramping angle α_{\max}	1.67 degrees
Series	Softcut®
$\varnothing D_3$	8 mm
Shank type	Plain shank
Setting angle κ	90 degrees
Milling application	End milling
Milling application	Ramping
Milling application	Circular milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Machining strategy	MTC
Tool exchange	PowerCard
Type of product	End / face mill

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/215609-10/2>