

**Digital height gauge and marking-out system, Marking height: 600mm****Order data**

Order number	445152 600
GTIN	4946368583334
Item class	44A

Description**Version:**

Direct reading from clear digital display. Battery operation with very low current consumption.

Data storage key – The measured result can be stored by pressing a key. All critical parts are hardened. Great stability by two parallel hardened columns with rack teeth on the inner faces (size. 1000 has 3 columns).

2 preset values permit reference values to be saved (e. g. granite table and workpiece).

Carbide tipped scriber. Sturdy base with hardened and lapped surface. Crank on the back of the display housing for quick adjustment and a hand wheel for fine adjustment.

Supplied with:

1 battery No. 081560 size 357, 1 cover, 1 carbide tipped scriber No. 443510.

Optional extras:

Square holder No. 445180 for holding dial indicators and lever indicators, centring gauge No. 445250, protractor No. 453500, holder No. 453520, and data cable No. 497080.

Technical description

Base length	180 mm
-------------	--------

Data sheet

Base width	120 mm
Marking height	600 mm
Error limit	0.05 mm
Scale divisions	0.005 mm
Battery life approx.	3500 h
#Article no of the battery / rechargeable battery fitted	081560 357
#Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Calibration	E1
Type of product	Height gauge and marking device

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/445152-600>