

**Value pack WNMG indexable insert medium machining 30 pieces HB7010-2****Order data**

Order number	GG2484 080408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.3 - 4 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting depth $a_{p \min}$	0.55 mm
Contents	252070 HB7010-2
Main application	P
Tool material	Carbide
ISO code indexable insert	WNMG 080408
Cutting depth $a_{p \max}$	2.75 mm
Cutting speed v_c main application	140 - 440 mm/min
Finishing/roughing assignment	Finishing
Number of changes/inserts	6

Corner radius	0.8 mm
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2484 080408