

Garant**CNMG indexable insert for medium machining 30 pieces, HB7140-2, Size: 120412****Order data**

Order number	GG2908 120412
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.8 mm
Coating	coated
ISO code indexable insert	CNMG 120412
Number of changes/inserts	4
Main application	M
Tool material	Carbide
Feed f	0.1 - 0.4 mm/rev.
Cutting depth a_p	0.5 - 4 mm
Contents	250160 HB7140-2
Cutting speed v_c main application	60 - 200 mm/min

Data sheet

Corner radius	1.2 mm
Cutting depth $a_{p \max}$	4:25 mm
Tolerance	M
Quantity	30
Finishing/roughing assignment	Finishing
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2908 120412