


Garant**Value pack solid carbide jobber drill extra short, 5 pieces****Order data**

Order number	GG1251 10,5
GTIN	4067263106562
Item class	GGN

Description**Version:**

With the same nominal and shank Ø.
 TiAlN coating for even better performance.
 Similar to DIN 6539 (extra-short).

Same as number: 122151.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.
 Non slip clamping in drill chuck No. 341050 with diamond coated clamping jaws.

Technical description

Tolerance nominal Ø	h7
recommended maximum drilling depth L_2	27.3 mm
Contents	5"
Feed f in steel < 1100 N/mm ²	0.14 mm/rev.
Nominal Ø D_c	10.5 mm
Shank Ø D_s	10.5 mm

Data sheet

Number of cutting edges Z	2
Standard	DIN 6539
Overall length L	89 mm
Flute length L _c	43 mm
Shank tolerance	h7
Coating	TiAlN
Tool material	Solid carbide
Type	N
Point angle	118 degrees
Helix angle	30 degrees
Shank	Parallel shank to h7
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	260 m/min	N
Aluminium (short chipping)	suitable	180 m/min	N
Alu > 10% Si	suitable	180 m/min	N
Steel < 500 N/mm ²	suitable	90 m/min	P
Steel < 750 N/mm ²	suitable	90 m/min	P
Steel < 900 N/mm ²	suitable	80 m/min	P
Steel < 1100 N/mm ²	suitable	60 m/min	P
Steel < 1400 N/mm ²	suitable	35 m/min	P
INOX < 900 N/mm ²	suitable	35 m/min	M
INOX > 900 N/mm ²	suitable	25 m/min	M

Data sheet

Ti > 850 N/mm ²	suitable	25 m/min	S
GG(G)	suitable	90 m/min	K
CuZn	suitable	180 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		

Suitable products

No Shop URL available for: GG1251 10,5