


Garant**Master Eco clamping toolholder short SVHCR 107.5°, for indexable inserts SV.., right****Order data**

Order number	261298 20/11
GTIN	4069515004541
Item class	21U

Description**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Set of insert screws	269023 1
Shank size	20 mm
Functional width L ₄	25 mm
ISO code toolholder	SVHCR/L 2020X11
Series	Master Eco
Standard	Works standard

Data sheet

Insert size	11 mm
suitable indexable insert	VC.. 1103..
Head length L ₁	35 mm
Overall length L	95 mm
Application type	right-hand
Through-coolant	yes
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

No Shop URL available for: 261298 20/11