

**Value pack DNMG indexable insert roughing 30 pieces HB7010-2****Order data**

Order number	GG2431 150608
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.25 - 0.6 mm/rev.
Contents	250862 HB7010-2
Main application	P
Cutting depth a_p	1.5 - 6 mm
Cutting depth $a_{p \max}$	3.75 mm
Corner radius	0.8 mm
Tool material	Carbide
Cutting speed v_c main application	120 - 415 mm/min
Cutting depth $a_{p \min}$	0.55 mm
Number of changes/inserts	4
ISO code indexable insert	DNMG 150608

Data sheet

Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2431 150608