


TCMT indexable insert for finishing 50 pieces, HB7120-1, Size: 110204
Order data

Order number	GG3543 110204
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.1 - 0.3 mm/rev.
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Main application	M
Quantity	50
Cutting depth a_p	0.2 - 1.5 mm
Tool material	Carbide
Number of changes/inserts	3
Cutting speed v_c main application	90 - 290 mm/min
ISO code indexable insert	TCMT 110204
Cutting depth $a_{p \max}$	2.75 mm
Contents	260952 HB7120-1
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3543 110204
