

Garant**VCMT indexable insert for finishing 50 pieces, HB7130-2, Size: 160402****Order data**

Order number	GG3568 160402
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	80 - 270 mm/min
Corner radius	0.2 mm
Number of changes/inserts	2
Cutting depth $a_{p \max}$	2.5 mm
Quantity	50
ISO code indexable insert	VCMT 160402
Tolerance	M
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.2 - 1.5 mm
Cutting depth $a_{p \min}$	0.15 mm
Main application	M

Contents	261370 HB7130-2
Tool material	Carbide
Finishing/roughing assignment	Finishing
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3568 160402