




## Solid carbide drill plain shank DIN 6535 HA, AlTiN-Si, Ø DC m7 (mm or inch): 10



### Order data

Order number	GG2771 10
GTIN	4062406989552
Item class	GGN

### Description

#### Version:

Tool specially matched to drilling holes without through-coolant. **Concave major cutting edges** and a **special flute profile** ensure a good chip evacuation. The sturdy cutter geometry with **special point geometry** and 4 cutting edges ensures drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely **wear-resistant** and **heat-resistant coating**.

**Same as No. 122771.**

**Form HB available with No. GG2772 at the same price.**

#### Note:

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

### Technical description

Overall length L	103 mm
Feed f in steel < 900 N/mm <sup>2</sup>	0.2 mm/rev.
recommended maximum drilling depth L <sub>2</sub>	46 mm
Flute length L <sub>c</sub>	61 mm

Nominal Ø D <sub>c</sub>	10 mm
Tolerance nominal Ø	m7
Shank Ø D <sub>s</sub>	10 mm
Standard	DIN 6537
Number of cutting edges Z	2
Contents	5
Coating	AlTiN-Si
Tool material	Solid carbide
Version	6xD
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	no
Colour ring	green
Type of product	Jobber drill

## User data

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Aluminium (short chipping)	suitable only under restricted conditions	200 m/min	N
Alu > 10% Si	suitable only under restricted conditions	160 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	90 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	80 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	70 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
GG	suitable	90 m/min	K
GGG	suitable only under restricted conditions	60 m/min	K

Uni	suitable
wet maximum	suitable
dry	suitable only under restricted conditions

---

## Accessories

Solid carbide drill plain shank DIN 6535 HA Ø DC m7 (mm or inch) 10

122771 10