

Garant**CNMG indexable insert for medium machining 50 pieces, HB7020-2, Size: 160608****Order data**

Order number	GG2411 160608
GTIN	4067263092384
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	5.5 mm
Tool material	Carbide
Main application	P
Cutting depth a_p	0.3 - 4 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.55 mm
Number of changes/inserts	4
Feed f	0.2 - 0.5 mm/rev.
Cutting speed v_c main application	130 - 370 mm/min
ISO code indexable insert	CNMG 160608

Contents	250168 HB7020-2
Corner radius	0.8 mm
Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2411 160608