

**DCMT indexable insert for medium machining 50 pieces, HB7120-1, Size: 070202****Order data**

Order number	GG3523 070202
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	1.75 mm
Cutting depth a_p	0.5 - 2.5 mm
Main application	M
Corner radius	0.2 mm
Cutting depth $a_{p \min}$	0.15 mm
Quantity	50
Feed f	0.1 - 0.4 mm/rev.
ISO code indexable insert	DCMT 070202
Tool material	Carbide
Cutting speed v_c main application	80 - 260 mm/min
Tolerance	M
Contents	260449 HB7120-1
Number of changes/inserts	2
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG3523 070202
