

**DNMG indexable insert for medium machining 30 pieces, HB7120-1, Size: 110404****Order data**

Order number	GG2924 110404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	80 - 260 mm/min
Feed f	0.2 - 0.5 mm/rev.
Cutting depth $a_{p \max}$	2.75 mm
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth a_p	0.5 - 5 mm
Contents	250752 HB7120-1
Main application	M
Tolerance	M
ISO code indexable insert	DNMG 150608
Corner radius	0.4 mm
Tool material	Carbide
Finishing/roughing assignment	Finishing
Number of changes/inserts	4
Quantity	30
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG2924 110404
