

Garant**WNMG indexable insert for medium machining 50 pieces, HB7140-2, Size: 080404****Order data**

Order number	GG2987 080404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Quantity	50
ISO code indexable insert	WNMG 080404
Coating	coated
Finishing/roughing assignment	Finishing
Contents	252068 HB7140-2
Tool material	Carbide
Cutting depth a_p	0.5 - 4 mm
Cutting speed v_c main application	60 - 200 mm/min
Corner radius	0.4 mm

Data sheet

Number of changes/inserts	6
Cutting depth $a_{p \max}$	2.75 mm
Feed f	0.1 - 0.5 mm/rev.
Tolerance	M
Main application	M
Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2987 080404